

ML 4700



SW

ACTIVE
SAFETY

OSAS



USAS



OPAS

Il nuovo codice sarà fornito solo ad esaurimento del vecchio

The new code will be supplied only when the old will be out of stock

Der neue Kode wird geliefert nur wenn der alte nicht mehr im Lager ist

Le nouveau code sera fourni uniquement lorsque le vieux stock sera écoulé

El nuevo código será suministrado sólo cuando el viejo está fuera de stock

O novo código irá ser fornecido apenas quando o antigo esgotar stock

easu
MANIFOLD

p. 241

* $F_{1i} =$


Isothermal
end force
at 100% Cu



p. 18


** $F_{1p} =$

Polytrophic
end force
at 100% Cu



 N2		°F 32 176	°C 0 80	ΔP ± 0,33 %/°C	P max 200 bar 2900 psi	P min 20 bar 290 psi	S 24,63 cm² 3.817 in²	SPM ~ 30 - 70 (at 20°C)	Max Speed 1,6 m/s	Maintenance kit 39BMML04700C								
CODE PHASING OUT from 05/2019	 NEW	Cu		L	L min		F0 Initial force		F1i * End force		F1p ** End force		V0			PED 2014/68/EU		
		mm	inch	mm	inch	mm	inch	daN	lb	daN	lb	daN	lb	cm³	in³	~Kg	~lb	
ML 4700 - 015 - C	ML 4700 - 015 - D	15	0.59	100	3.94	85	3.35	4925	11071	6966	15660	7856	17661	159,0	9.70	1,72	3.79	✓
ML 4700 - 025 - C	ML 4700 - 025 - D	25	0.98	120	4.72	95	3.74	± 5%		7858	17665	9085	20424	205,0	12.51	1,90	4.19	✓
ML 4700 - 038 - C	ML 4700 - 038 - D	38	1.50	150	5.91	112	4.41	200 bar		8432	18956	9891	22236	278,0	16.96	2,17	4.78	✓
ML 4700 - 050 - C	ML 4700 - 050 - D	50	1.97	180	7.09	130	5.12	2900 psi		8651	19448	10201	22933	353,0	21.53	2,44	5.38	✓
ML 4700 - 063 - C	ML 4700 - 063 - D	63	2.48	210	8.27	147	5.79			8929	20073	10598	23825	425,0	25.93	2,72	6.00	✓
ML 4700 - 080 - C	ML 4700 - 080 - D	80	3.15	250	9.84	170	6.69	+20 °C +68 °F		9155	20581	10922	24554	523,0	31.90	3,08	6.79	✓

KIT FOR LINKING



code: 39FML04700B



Seal (1x)



Washer (6x)



Screw (3x)



Bottom base (1x)





Instructions




Sostituire ogni 1.000.000 di cicli.
Replace every 1 million cycles.
Nach 1 Mio. Hübe austauschen.
Reemplazar a cada 1 millón de ciclos.
Substituir a cada 1 milhão de ciclos.


Bottom base dimension




Drop-In



Bottom mount - FB 75
FBA 75 - FBB 75
FBC 75 - FBD 75



FSA 75 - FSD 75
FSE 75



FSD 75 + R 75 A
FSE 75 + R 75 A



HOW TO ORDER



INSTALLATION GUIDELINE

